

Optimize your production

With the Cenomic Optima conversion set, Bühler offers process engineering-based optimization of your production. With the base kit, a Cenomic Optima adaptation is carried out on the agitator and product outlet. Additionally, individual conversion packages are selectable according to the condition of the machines:

- Ceramic inner lining
- Pulling-off device
- Optional increased drive
- And more

The benefits of Cenomic Optima technology generate 25% higher productivity* and temperature-protected grinding due to processing unit optimization. Minimized blockages and grinding media pressures continuously.



*Depending on product



Capacity

- Higher rate of production due to larger sieve area
- Better separation of grinding media
- Flow-optimized processing zone



Innovation

- Optimized dimensional characteristics in the processing zone
- More effective grinding
- Narrower distribution of particle sizes



Quality

- Larger sieve surface
- Minimal sieve blockage
- Constant product quality



Cenomic Optima - Conversion set




Optional: Pulling-off device for grinding container (recommended for ceramic inner lining)



Optional: Ceramic inner lining



Optional: 30 kW drive unit



Larger sieve in container lid

If you have any questions regarding this service or our service portfolio in general, feel free to mail us at cs.gd@buhlergroup.com



The direct line to our specialists:

Technical support: T +49 (0) 6023 9194 499 Spare parts: T +49 (0) 6023 9194 423



Bühler Alzenau GmbH – Business Area Grinding & Dispersing

Siemensstr. 88 T+49 (0) 6023 9194 402 D-63755 Alzenau, Germany F+49 (0) 6023 9194 444 cs.gd@buhlergroup.com buhlergroup.com

